



TTI

TURBO TEEJET INDUCTION

잡초 방제에 최적화된 침투성과 비산 완화 극대화



PWM
승인

장점

- JKI에서 승인한 90% 비산 감소 노즐*
- 표준 부채꼴 팬 스프레이 노즐보다 더 적은 미세 비산
- 마모를 줄이기 위해 사전에 둥글게 교정된 오리피스
- 사전 조립된 노즐 이용 가능
- 15° 분사 각도로 침투력 향상
- 침투성 제초제 분사에 특화

*자세한 내용은 추가 정보 항목의 JKI 등급 표를 참조하십시오.

특징



스프레이 분사 패턴 각도:
110°



작동 압력 범위:
1 bar ~ 7 bar



제작 가능한 재질:
VP- 폴리머

추가 정보



권장 압력:
2,5 ~ 4 bar

JKI
등급

비산 감소율 (%)

JKI 등급	비산 감소율 (%)		
	50%	75%	90%
TTI11002	2,0 - 5,0	2,0 - 2,5	-
TTI110025	1,5 - 5,0	1,5 - 2,5	1,5
TTI11003	1,5 - 5,0	1,5 - 2,5	1,5
TTI11004	1,0 - 5,0	1,0 - 3,0	1,0 - 2,0
TTI11005	1,0 - 5,0	1,0 - 3,0	1,0 - 2,0
TTI11006	1,0 - 7,0	1,0 - 4,0	1,0 - 3,0



사용량: L/ha

노즐 간격: 50cm

bar	입자 크기	용량 L/분	속도 (km/h)											스트레이너 메쉬 사이즈	캡 & 가스켓	
			5	6	7	8	10	12	14	16	18	20	25			
TTI110001	1.0	UC	0.23	55.2	46.0	39.4	34.5	40.8	27.6	19.7	23	17.3	15.3	11.0	100	115835A-8-CELR
	2.0	UC	0.32	76.8	64.0	54.9	48.0	57.6	38.4	27.4	32.0	24.0	21.3	15.4		
	3.0	XC	0.39	93.6	78.0	66.9	58.5	70.8	46.8	33.4	39.0	29.3	26.0	18.7		
	4.0	VC	0.45	108	90.0	77.1	67.5	81.6	54.0	38.6	45.0	33.8	30.0	21.6		
	5.0	VC	0.50	120	100	85.7	75.0	91.2	60.0	42.9	50.0	37.5	33.3	24.0		
	6.0	VC	0.55	132	110	94.3	82.5	99.6	66.0	47.1	55.0	41.3	36.7	26.4		
	7.0	C	0.60	144	120	103	90.0	108	72.0	51.4	60.0	45.0	40.0	28.8		
TTI110015	1.0	UC	0.34	81.6	68.0	58.3	51.0	40.8	34.0	29.1	25.5	22.7	20.4	16.3	100	115835A-5-CELR
	2.0	UC	0.48	115	96.0	82.3	72.0	57.6	48.0	41.1	36.0	32.0	28.8	23.0		
	3.0	XC	0.59	142	118	101	88.5	70.8	59.0	50.6	44.3	39.3	35.4	28.3		
	4.0	XC	0.68	163	136	117	102	81.6	68.0	58.3	51.0	45.3	40.8	32.6		
	5.0	VC	0.76	182	152	130	114	91.2	76.0	65.1	57.0	50.7	45.6	36.5		
	6.0	VC	0.83	199	166	142	125	99.6	83.0	71.1	62.3	55.3	49.8	39.8		
	7.0	VC	0.90	216	180	154	135	108	90.0	77.1	67.5	60.0	54.0	43.2		
TTI11002	1.0	UC	0.46	110	92.0	78.9	69.0	55.2	46.0	39.4	34.5	30.7	27.6	22.1	50	115835A-6-CELR
	2.0	UC	0.65	156	130	111	97.5	78.0	65.0	55.7	48.8	43.3	39.0	31.2		
	3.0	XC	0.79	190	158	135	119	94.8	79.0	67.7	59.3	52.7	47.4	37.9		
	4.0	XC	0.91	218	182	156	137	109	91.0	78.0	68.3	60.7	54.6	43.7		
	5.0	VC	1.02	245	204	175	153	122	102	87.4	76.5	68.0	61.2	49.0		
	6.0	VC	1.12	269	224	192	168	134	112	96.0	84.0	74.7	67.2	53.8		
	7.0	VC	1.21	290	242	207	182	145	121	104	90.8	80.7	72.6	58.1		
TTI110025	1.0	UC	0.57	137	114	97.7	85.5	68.4	57.0	48.9	42.8	38.0	34.2	27.4	50	115835A-10-CELR
	2.0	UC	0.81	194	162	139	122	97.2	81.0	69.4	60.8	54.0	48.6	38.9		
	3.0	XC	0.99	238	198	170	149	119	99.0	84.9	74.3	66.0	59.4	47.5		
	4.0	XC	1.14	274	228	195	171	137	114	97.7	85.5	76.0	68.4	54.7		
	5.0	VC	1.28	307	256	219	192	154	128	110	96.0	85.3	76.8	61.4		
	6.0	VC	1.40	336	280	240	210	168	140	120	105	93.3	84	67.2		
	7.0	VC	1.51	362	302	259	227	181	151	129	113	101	90.6	72.5		
TTI11003	1.0	UC	0.68	163	136	117	102	81.6	68.0	58.3	51.0	45.3	40.8	32.6	50	115835A-4-CELR
	2.0	UC	0.96	230	192	165	144	115	96.0	82.3	72.0	64.0	57.6	46.1		
	3.0	XC	1.18	283	236	202	177	142	118	101	88.5	78.7	70.8	56.6		
	4.0	XC	1.36	326	272	233	204	163	136	117	102	90.7	81.6	65.3		
	5.0	VC	1.52	365	304	261	228	182	152	130	114	101	91.2	73.0		
	6.0	VC	1.67	401	334	286	251	200	167	143	125	111	100	80.2		
	7.0	VC	1.80	432	360	309	270	216	180	154	135	120	108	86.4		
TTI11004	1.0	UC	0.91	218	182	156	137	109	91.0	78.0	68.3	60.7	54.6	43.7	50	115835A-3-CELR
	2.0	UC	1.29	310	258	221	194	155	129	111	96.8	86.0	77.4	61.9		
	3.0	XC	1.58	379	316	271	237	190	158	135	119	105	94.8	75.8		
	4.0	XC	1.82	437	364	312	273	218	182	156	137	121	109	87.4		
	5.0	VC	2.04	490	408	350	306	245	204	175	153	136	122	97.9		
	6.0	VC	2.23	535	446	382	335	268	223	191	167	149	134	107		
	7.0	VC	2.41	578	482	413	362	289	241	207	181	161	145	116		
TTI11005	1.0	UC	1.14	274	228	195	171	137	114	97.7	85.5	76.0	68.4	54.7	50	115835A-7-CELR
	2.0	UC	1.61	386	322	276	242	193	161	138	121	107	96.6	77.3		
	3.0	XC	1.97	473	394	338	296	236	197	169	148	131	118	94.6		
	4.0	XC	2.27	545	454	389	341	272	227	195	170	151	136	109		
	5.0	VC	2.54	610	508	435	381	305	254	218	191	169	152	122		
	6.0	VC	2.79	670	558	478	419	335	279	239	209	186	167	134		
	7.0	VC	3.01	722	602	516	452	361	301	258	226	201	181	144		
TTI11006	1.0	UC	1.37	329	274	235	206	164	137	117	103	91.3	82.2	65.8	50	115835A-9-CELR
	2.0	UC	1.94	466	388	333	291	233	194	166	146	129	116	93.1		
	3.0	XC	2.37	569	474	406	356	284	237	203	178	158	142	114		
	4.0	XC	2.74	658	548	470	411	329	274	235	206	183	164	132		
	5.0	VC	3.06	734	612	525	459	367	306	262	230	204	184	147		
	6.0	VC	3.35	804	670	574	503	402	335	287	251	223	201	161		
	7.0	C	3.62	869	724	621	543	434	362	310	272	241	217	174		

참고: 항상 도포량을 더블체크하십시오. 표는 21°C에서의 물 분사를 기준으로 작성되었습니다. 입자 크기 데이터는 ISO 25358을 기준으로 합니다.

입자 크기 분류

C
굵음

VC
매우굵음

XC
극도로 굵음

UC
가장 굵음

최적의 분사 높이

각도
110°

노즐 간격

50 cm

50 cm

25 cm

25 cm

주문 방법

소재 코드 (VP = 폴리머)

노즐 타입

TTI

110

04

VP

-CE

선택사항

분사 각도 (110°)

용량 크기

캡 및 가스켓 포함

